

TECHNICAL DATA SHEET

Part#: 40PH

Hemostats - 8" 30°Curved - SS - Vinyl-Coated Handle
Ideal for clamping parts for inspection

The 40PH stainless steel locking hemostat with 30°curved serrated jaws has vinyl-coated handles. The overall length is 8".

• Precision Level	★★
• Material	SS (AISI 440)
• Surface Resistivity	Insulative
• Shape	Curved
• Tip Size	
• Tip Angle	30°
• Tip Length	
• Body Width	.283" (7.08mm)
• Body Height	.06" (1.5mm)
• OAL	8" (200 mm)
• Weight (OZ)	2
• UPC	662847010729
• Schedule B	9018.90.80.00
• ECCN	EAR99
• UNSPSC Code	42151685
• Country of Origin	Pakistan
• Group	Curved - Vinyl Handles

