

TECHNICAL DATA SHEET

Part#: 14A-GW

Tweezers - Cutting - Mini 80°Angulated - Carbon Steel
Designed to be lightweight and easy to handle

The 14A-GW 80°angulated slim cutting tweezers has a new, thinner body designed to be lightweight and easy to handle. The cutting capacity is 0.010" soft wire. The overall length is 4.38". It is made of carbon steel with flame hardened edges.

| | |
|-----------------------|-----------------|
| • Precision Level | ★★★ |
| • Material | Carbon Steel |
| • Surface Resistivity | Conductive |
| • Shape | Angulated |
| • Tip Size | .210" (5.25mm) |
| • Tip Angle | 80° |
| • Tip Length | |
| • Body Width | 0.393" (9.83mm) |
| • Body Height | .06" (1.5mm) |
| • OAL | 4.38" (110mm) |
| • Weight (OZ) | 1.5 |
| • UPC | 662847003295 |
| • Schedule B | 8203.20.20.00 |
| • ECCN | EAR99 |
| • UNSPSC Code | 27112105 |
| • Country of Origin | Switzerland |
| • Group | Miniature Heads |

