

TECHNICAL DATA SHEET

Part#: 15A-RW-M

Tweezers - 3 Star Cutting - 15A-RW Series - Carbon Steel - Medical Grade
General purpose cutting of small wires or flashing. The epoxy coating has been removed to prevent contamination.

The 15A-RW-M 70°angulated round tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". The cutting blade is much shorter than the 15A-GW and the top of the head has been rounded for better visibility. The 'M' signifies MEDICAL GRADE.

• Precision Level	★★★
• Material	Carbon Steel
• Surface Resistivity	Conductive
• Shape	Angulated
• Tip Size	.095" (2.38mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.393" (9.83mm)
• Body Height	.10" (2.50mm)
• OAL	4.5" (112.5mm)
• Weight (OZ)	1.5
• UPC	662847003400
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Relieved Round Head (15A-RW)

