

TECHNICAL DATA SHEET

Part#: 213D-N

Brushes - Cleanroom Safe - Straight - ★★★ - SS/Statio09 Bristles

The 213D-N three star clean room safe brush has stainless steel handles and new Statigo9 fiber bristles. The bristles are mechanically clamped into the handle for maximum fiber retention. The fibers are similar to nylon, except they are static dissipative (10^8 ohms/sq.).

- Precision Level ★★★
- Material SS Handle/Horse Hair Bristles
- Surface Resistivity 10^8 ohms/sq
- Shape Straight
- Group Brushes
- Angle n/a
- Body Width 0.375" (9.38mm)
- Body Height 0.38" (9.5mm)
- OAL 6" (150mm)
- Weight (OZ) 1.2
- UPC 662847005176
- Schedule B 9603.90.99.00
- ECCN EAR99
- UNSPSC Code
- Country of Origin USA

