



Main

Range	Thalassa
Accessory / separate part category	Fixing accessory
Product or component type	Wall fixing support
Anwendung	Multi-purpose
Nennmaße des Gehäuses	4.57 in (116 mm) 4.57 in (116 mm) 2.44 in (62 mm)
Mounting location	Top and bottom, on rear of the enclosure
Range compatibility	Thalassa TBP Thalassa TBS
Device composition	4 lug screw

Complementary

Material	plastic
Fixing mode	Screwed - from the outside
Permanent permissible load	66.14 Lb(US) (30 kg) on the body 22.05 Lb(US) (10 kg) on the cover
Height	100 mm
Width	3.54 in (90 mm)
Depth	0.79 in (20 mm)
Net Weight	0.07 lb(US) (0.03 kg)



Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901377429
Nbr. of units in pkg.	1
Package weight(Lbs)	0.07 lb(US) (0.03 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	1.69 in (4.3 cm)
Package 1 Length	3.46 in (8.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
