

T-adapter FB-TA-M12-5POL

Part number: 171175

FESTO



Data sheet

Feature	Value
Type code	FB-TA
Type of mounting	With through-hole
Electrical connection	5-pin M12x1/M12x1 Plugs/sockets
DC operating voltage range	10 V ... 30 V
Current rating	4 A
Degree of protection	IP67
Ambient temperature	-25 °C ... 90 °C