



## T5655 N-Vision

Eye protection



Description:	Next generation safety and sports spectacle with face-fitting curve and soft nose piece for maximum comfort. Equipped with two types of temples; adjustable hockey and straight sports temples. Engineered to adapt a RX prescription insert.		
Materials:	Lens	– Curve 9 based polycarbonate lens 4A-coated; Anti-scratch, Anti-mist, Anti-static and Anti-UV Colours: Clear, Smoke, Amber, In/ Outdoor	
	Frame	– TR90 nylon, Blue, Black or Grey.	
	Nose piece	– Clear Soft PVC	
	Hinge pivot	– Stainless steel	
Weight:	30 gr.		
Standards:	Frame	– EN166	<b>N</b> F
	Lens	– EN166	<b>N</b> 1F
		– EN170 UV 2-1,2	<b>N</b> 1F (Clear, Amber)
		– EN170 UV 2-1,7	<b>N</b> 1F (In/ Outdoor)
		– EN172 5-3,1	<b>N</b> 1F (Smoke)
Technical Performance	Impact resistance	– 6mm steel ball at 45m/s.	
	Visible light transmission	– 92% minimum	
	UV ABC absorption	– 100% up to 390nm	
	Heat resistance	– up to 80°C.	
	Abrasion resistance	– conforms to EN166 requirement	
Application:	Protects against impacts from flying particles of increased robustness in accordance with cited standards.		
Options:	<ul style="list-style-type: none"> <li>- RX Insert for prescription lenses</li> <li>- Cases :204508, 204512, 204513, 84</li> <li>- Cords :204522, 204520, 608010, 608011 and 608012</li> <li>- Spare lenses :606790, 606791, 606792 and 493HRL</li> <li>- Nose piece :208590</li> <li>- Cleaning :LCS2, T1025T, 10204</li> </ul>		
Packaging:	Individual polyethylene bags in boxes of 10		