

0230023204 Power 150

## Compressor Power 150



- Compact and mobile piston compressor for professional use indoors and at construction sites
- Oil-less piston condenser with innovative PLS technology
- For single phase alternating current
- Fittings and control elements protected in tubular frames and clearly visible
- Two manometers for controlled working and tank pressure
- Pressure reducer for controlled working pressure
- Thermal motor protection
- Brand quick-action coupling
- 10 years tank warranty against rusting
- Built according to CE guidelines
- Portable assembly compressor – ideal for tackers and nails as well as for separating pipes by force
- Slow rotating motor, especially low noise and vibration
- Can be transported horizontally
- Carrying handle with rubber-coating
- Vibration-damping suction base

### Comparative device characteristics

Suction rate	100 l/min
Capacity	50 l/min
Effective delivery volume (at 7.2 bar working pressure)	46 l/min
Maximum pressure	8 bar
Rated input power	0,75 kW
Maximum speed	1.450 /min
Tank capacity	3 l
Voltage	230 V
Sound pressure level (LpA)	74 dB(A)
Dimensions	465 x 310 x 465 mm
Weight	16 kg