

## Han Q 8/0 - GS - Metal



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 008 0502
Specification	Han Q 8/0 - GS - Metal
HARTING eCatalogue	<a href="https://b2b.harting.com/19120080502">https://b2b.harting.com/19120080502</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for Han-Compact® half cable gland for Han® Q 8/0 Crimp (max. 400 V), Han® Q17/0 and Han® Q Data RJ45

### Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Side entry
Cable entry	1x M25
Field of application	Hoods/Housings for higher EMC requirements

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 No. 182.3 PVVA8.E318390
CE	Yes

## Commercial data

Packaging size	1
Net weight	163.76 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors