

## Han 3HvE-gs-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 34 003 0520
Specification	Han 3HvE-gs-M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19340030520">https://b2b.harting.com/19340030520</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han Hv E <sup>®</sup>
Type of hood/housing	Hood
Type	Low construction

### Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	1x M20
Field of application	Special hoods/housings for Han Hv E <sup>®</sup> screw terminal

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant



Pushing Performance

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	143.7 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors