



Jigsaw blade T 318 B



Technical Data

**Part no.:** 2 608 631 404

Packaging type	Paper / Cardboard / Corrugated board - Packaging, folded carton, with Euro hole
Sales package qty	5 Units
Despatch package qty	1 Units

**Description**

**T 318 BF**

HSS, wavy set, milled

Medium-thick sheet metal (2.5-6 mm), pipes +profiles inc. aluminium (dia. <65 mm), precise angle cut

**Areas of application**

Metal plates [mm]	2,5-6
Pipes, profiles: closed [mm]	<65
Aluminium [mm]	<65

**Details**

Material	HSS
Tooth design	wavy set, milled
Length of teeth [mm]	106
Tooth spacing [mm]	2
Areas of application	Medium-thick sheet metal (2.5-6 mm), pipes +profiles inc. aluminium (dia. <65 mm)

