

Han 16B-Hood Top Entry-M50



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 016 0429
Specification	Han 16B-Hood Top Entry-M50
HARTING eCatalogue	https://b2b.harting.com/19300160429

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hood
Description of hood/housing	Special type
Type	High construction

Version

Locking type	Double locking lever
Size	16 B
Version	Top entry
Cable entry	1x M50
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------



Pushing Performance

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
CE	Yes

Commercial data

Packaging size	1
Net weight	334 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors