




Order Code	TCK-096
Inductance (each winding)	160 μ H \pm 35% (at 100 kHz / 100 mV)
Impedance (DCR)	7 m Ω max.
Rated Current	7.84 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	12.5 max.
B	12.5 max.
C	10.7 max.
D	2.5 min
E	7.62 \pm 0.2
F	7.62 \pm 0.2
G	\varnothing 0.6 \pm 0.1