


Inductor TCK-120


| Order Code            | TCK-120                              |
|-----------------------|--------------------------------------|
| Inductance            | <b>10 μH ±20%</b> (at 100 kHz / 1 V) |
| Impedance (DCR)       | 354 mΩ max.                          |
| Rated Current         | 0.9 A max.                           |
| Operating Temperature | -40°C to +125°C                      |



## Impedance Curve



## **Outline Dimensions**



| Dimensions [mm] |     |
|-----------------|-----|
| а               | 1.9 |
| b               | 3.6 |
| С               | 2.7 |