


Inductor TCK-121


Order Code	TCK-121
Inductance	15 μH ±20% (at 100 kHz / 1 V)
Impedance (DCR)	570 mΩ max.
Rated Current	0.7 A max.
Operating Temperature	-40°C to +125°C



Impedance Curve



Outline Dimensions



Dimensions [mm]	
а	1.9
b	3.6
С	2.7

Page 1 / 1