
TRACO POWER

Inductor


Order Code	TCK-161
Inductance	150 μH ±20% (at 100 kHz / 1 V)
Impedance (DCR)	1548 mΩ max.
Rated Current	0.32 A max.
Operating Temperature	-40°C to +125°C


Impedance Curve



Frequency (MHz)

Outline Dimensions





 Dimensions [mm]

 A
 5.3 ±0.4

 B
 5.0 ±0.4

 C
 2.7 ±0.5

 D
 2

 E
 2

 F
 2

© Copyright 2021 Traco Electronic AG

TRACO POWER

TCK-161

