

## Twist-Lock® Devices

### 20A, 480V AC, 3 Phase, 3 Pole, 4 Wire Grounding Spring Termination Single Flush Receptacle

#### Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

#### Ordering Information

Description	Device Color	UPC	Catalog Number
Nylon face, back and side wire.	Black	783585788579	HBL2430ST

#### Listings

Listed to UL 498  
Certified to CSA C22.2 No.42

#### Specifications

Face	Nylon
Base	Nylon
Contacts	Brass
Spring	Steel
Mounting Strap	Brass

#### Performance

##### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

##### Mechanical

Terminal Accommodation	Solid/Stranded #14 AWG to #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498

##### Environmental

Flammability	V2 or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)

# HUBBELL



#### Accessories

	HBL2431
Wallplate or Weatherproof Cover	1.60" Opening
Switched Enclosure	SETL3

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

