



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,
Ming-Chung Rd., Hsin-Tien Dist,
New Taipei City, Taiwan, R.O.C. Post code: 23114
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722

<http://www.prokits.com.tw> Email: sales-c@mail.prokits.com.tw

PRODUCT SPECIFICATION

PK-1700NA Electronic Master Kit (with NEMA plug)



*** Picture for reference only. All specifications are subject to change by supplier. ***

Specifications:

PK-1700NA(Inch) Contents	
103-132C	Utility component storage box
1PK-051DS	Dual Color Lineman's Plier(205mm)
1PK-067DS	Dual Color Side CuttingPlier (165mm)
1PK-108T	Reverse Action Tweezer (Self-Gripping) (165mm)
1PK-709DS	Dual Color Long Nose Plier (166mm)
1PK-H026	Adjustable Wrench - 6"
8PK-3161	7 In 1 Crimping Tool

8PK-366N-G	Desoldering Pump
908-609	IC Extractor
9DP-031B	Desoldering wick(2.0mm)Length(1.5M)
9DP-3616A	Square scraper/Stainless steel brush
9DP-3616B	Slotted shaft/Split 45 lever
9DP-3616C	Tapered reamer/Tapered needle
9DP-S001	Pen Solder 63%
SI-130A-20	Ceramic soldering iron 110V
9SD-200-I1	Pro-Soft Screwdriver 3/16"(inch)
9SD-200-I2	Pro-Soft Screwdriver 1/4"(inch)
9H003	3 Prong Holder
9HW-7106B	Double Open End Wrench 6x7mm
9HW-7108B	Double Open End Wrench 8x10mm
9HW-7111B	Double Open End Wrench 11x13mm
9HW-7112B	Double Open End Wrench 12x14mm
9HW-7114B	Double Open End Wrench 14x17mm
9HW-7117B	Double Open End Wrench 17x19mm
9K003A-1	Needle File Flat
9K003B-1	Needle File Round
9K003C-1	Needle File Square
9K003D-1	Needle File Triangle
9K003E-1	Needle File Semicircle
9MS-001	PVC Insulated Tape
9PK-153	Brush Black Handle
9SD-201A	Pro-Soft Screwdriver (-3.0 3.0x75mm)
9SD-201B	Pro-Soft Screwdriver (+#0 3.0x75mm)
9SD-202A	Pro-Soft Screwdriver (-5 5x75mm)
9SD-202B	Pro-Soft Screwdriver (+#1 5x75mm)
9SD-207A	Pro-Soft Screwdriver (-6 6x100mm)
9SD-207B	Pro-Soft Screwdriver (+#2 6x100mm)

9SD-220A	Pro-Soft Screwdriver (-6 6x40mm)
9SD-220B	Pro-Soft Screwdriver (+#2 6x40mm)
SH-1025	Soldering Tip Cleaner
DK-2039	Utility Knife (3 Blades Self Loading)
DK-2040	Measuring Tape (3M/10FT)
HW-121M/8PK-021NA	Folding Type Hex Key Set(Metric or inch)
MS-391	Inspection Mirror
NT-309	Smart Non-Contact Voltage Tester
PD-2606	Heavy Duty Curved-Claw Hammer W/Fiberglass Handle
PM-736	Long Nose Plier (132mm)
PM-737	Diagonal Cutting Plier (109mm)
PM-755	Bent Nose Plier (135mm)
PN-P010N	Slip-Channel Pump Plier 10" (254mm)
SD-081-P2	Precision Screwdriver(No.00 x 50mm)
SD-081-P5	Precision Screwdriver(No.0 x 75mm)
SD-081-P7	Precision Screwdriver(No.1 x 150mm)
SD-081-S3	Precision Screwdriver(-2.0 x 50mm)
SD-081-S6	Precision Screwdriver(-2.4 x 75mm)
SD-081-S7	Precision Screwdriver(-3.0 x 100mm)
SR-336	Multi Purpose Scissor
9PK-1900N-P	Pallet for PK-1900N series
9PK-1900N-TP	Top Pallet for PK-1900N series
TC-756	Deluxe Aluminum Frame Tool Case

Product Weight (w/o package) :

Weight(Kg)	Measurement		
	L(mm)	W(mm)	H(mm)
8.5kgs	470	370	170

Individual Packing

Packing :

Master Packing :

	Pcs	Kg	Kg	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	8.5	47	37	17	-
Inner Box	1		8.5	47	37	17	-
CTN	2	17	18	50.7	40	37.5	2.7

~ THE END ~