

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2175112101](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead L1NK 250 Female-to-L1NK 250 Female, Tin (Sn) Plating, 75.00mm Length, 26 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|---|
| Product Family | Cable Assemblies |
| Series | 217511 |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | L1NK 250 Crimp Terminals |
| Overview | Off-the-Shelf Pre-Crimped Leads |
| Product Name | L1NK 250 |
| UPC | 195842119659 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 75.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Red |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | PVC |
| Net Weight | 0.299/g |
| Packaging Type | Bag |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.42mm-1.60mm |
| Wire Size AWG | 26 |
| Wire/Cable Type | UL 1569 |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 6.5A |
| Voltage - Maximum | 250V AC (RMS)/DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2175112101-000 |
|---------------|----------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[217511 Series](#)

Use With

L1NK 250 Receptacle Housing [207841](#)