



Main

| | |
|--------------------------|---------------------------------------|
| Range | Spacial |
| Product name | Spacial SBX |
| Device application | Multi-purpose |
| Category | Industrial box |
| Device short name | SBX |
| Enclosure type | Flat face box |
| Enclosure nominal height | 150 mm |
| Enclosure nominal width | 150 mm |
| Enclosure nominal depth | 80 mm |
| Enclosure mounting | Wall mounted |
| Device composition | 4 cover screw 1 cover 1 body |
| Body type | Single piece body folded and welded |
| Type of front cover | Plain door |
| Cover fixing | Half turn metal screw |
| Lock type | Captive screw PZ2 outside sealed area |
| Removable parts | Cover by captive screws |

Complementary

| | |
|-------------------------|------------------------------|
| Material | Stainless steel 304L |
| Surface finish | Scotch-Brite® brushed |
| Standards | IEC 62208 |
| Product certifications | BV BVM UL |
| IP degree of protection | IP66 conforming to IEC 60529 |

| | |
|-------------------------------------|------------------------------|
| IK degree of protection | IK10 conforming to IEC 62262 |
| Ambient air temperature for storage | -35...60 °C |
| Operating temperature | -35...80 °C |
| Net weight | 1.1 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 1.114 kg |
| Package 1 Height | 17 cm |
| Package 1 width | 17 cm |
| Package 1 Length | 10 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |



Main

| | |
|------------------------------------|--------------------|
| Anwendung | Multi-purpose |
| Range | Spacial |
| Product or component type | Rail |
| Accessory / separate part category | Mounting accessory |
| Type of rail | Symmetrical DIN |
| Enclosure nominal dimensions | - |
| Mounting support | Self-tapping screw |
| Range compatibility | Spacial SBM |
| Device composition | 1 rail |
| Quantity per set | Set of 10 |

Complementary

| | |
|----------------|--|
| Material | Steel |
| Surface finish | Zinc coated |
| Fixing mode | By screw - screw type Ø5 mm self-tapping screws - rear of enclosure location |
| Height | 35 mm |
| Width | 135 mm nominal: 114 mm fixing centers: |
| Depth | 7.5 mm |
| Thickness | 1 mm |
| Net weight | 0.045 kg |

Packing Units

| | |
|------------------------------|------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 45 g |

| | |
|------------------|--------|
| Package 1 Height | 14 cm |
| Package 1 width | 4.5 cm |
| Package 1 Length | 4.5 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |