

Long Nitrosolve™ Z51G

Chemical resistance



For solvent handling

This nitrile glove provides **protection** against many solvents and oil based chemicals.


Nitrile gloves are ideal for a range of **industrial environments**. The Z51G is a longer, elbow length gauntlet style glove with flock lining for comfort in extended use.

Suggested ideal applications

automotive industry, petrochemicals, chemical industry, printing



CE 0086





Long Nitrosolve™ Z51G

Glove specifications


Glove reference	Material/ lining	Finish	Colour	Size	Average length (mm)	Average palm thickness (mm) (Double wall)	Performance Level EN 420:1994	Performance Level EN 388:1994 Mechanical hazards	Performance Level EN 374:1994 Chemical hazards	Performance Level EN 374:1994 Micro-organism hazards
Long Nitrosolve™ Z51G	Flocked nitrile	Raised grip pattern	Green	8 (M), 9 (L), 10 (XL)	435	1.12	Dexterity: 5	4102		

Key features and benefits

- Nitrile rubber
- Flocked
- Heavy duty construction
- Long elbow length cuff
- Manufactured using a quality assurance system under the control of the BSI
- CE Complex design
- Very good abrasion resistance and protection from oils based chemicals and solvents
- For greater comfort
- Durable and hard wearing
- Extra protection

Key to EN Scores

Where 0 indicates test performance below level 1
Where an X appears in the sequence, no test was carried out

EN 388:1994	Resistance to abrasion	0-4
	Blade cut resistance	0-5
	Tear resistance	0-4
	Puncture resistance	0-4

These gloves comply with the main requirements of the European Personal Protective Equipment Directive (Directive 89/686/ECC) dated 21st December 1989. They are subjected to CE-standard examinations, which are carried out by a notified laboratory, BSI, which certifies that these gloves comply with the applicable EN standards, and attests to the performance standards obtained during testing.

For the latest information, please visit our website
marigold-industrial.com

F
Marigold Industrial
5, Allée des Bas Tilliers
92238 Gennevilliers Cedex - France
Tel: + 33 (0)1 47 92 92 92
Fax: + 33 (0)1 47 92 92 19
france@marigold-industrial.com

CDN
Tel: + 1 866 669 1202
Fax: + 1 866 669 1704
canada@marigold-industrial.com

FIN
Tel: + 358 (0) 71 777 1000
Fax: + 358 (0) 71 777 1001
finland@marigold-industrial.com

P
Tel: + 351 239 429070
Fax: + 351 239 429079
portugal@marigold-industrial.com

A, CH, D, EASTERN EUROPE
Tel: + 43 (0)1 263 87 22
Fax: + 43 (0)1 263 87 22 20
austria@marigold-industrial.com

DK
Tel: + 45 48 24 60 23
Fax: + 45 48 24 53 23
denmark@marigold-industrial.com

I
Tel: + 39 02 45703575
Fax: + 39 02 45703595
italia@marigold-industrial.com

UK, IRL, N, S
Tel: + 44 (0) 1454 323633
Fax: + 44 (0) 1454 324366
uk@marigold-industrial.com

B, LUX, NL
Tel: + 32 (0)2 7114545
Tel: + 31 (0) 486 412150
Fax: + 32 (0)2 7114549
benelux@marigold-industrial.com

ESP
Tel: + 34 (96) 661 30 30
Fax: + 34 (96) 545 02 40
iberia@marigold-industrial.com

MY, ASIA PACIFIC
Tel: + 604 4891 973
Fax: + 604 4891 048
malaysia@marigold-industrial.com.my

USA
Tel: + 1 866 343 7025
usa@marigold-industrial.com

