


KERN ACS80-4



The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]



Reference weight: yes

Functions

Counting function: yes
Function to save totals: yes
Percentage determination: yes
Standby function: yes
Weighing with tolerance range: yes

Environmental conditions

Maximum humidity: 85 %
Maximum operating temperature: 30 °C
Minimum ambient temperature: 10 °C
Minimum humidity: 20 %

Power supply

Input voltage: 110 V - 230 V AC
Mains adapter: Mains adapter external
Mains adapter/adapter included: EURO CH UK US

Services (optional)

DAkkS Certificate: 963-101

Category

Brand: KERN
Category: Balances
Product Group: Analytical balance

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 390 x 565 x 520 mm
Gross weight: 8,900 kg
Net weight: 6,100 kg
Shipping method: Parcel service

Construction

Casing material: Plastic
Dimensions draft shield (WxDxH): 201 x 220 x 256 mm
Dimensions housing (WxDxH): 210 x 340 x 325 mm
Level indicator: yes
Material weighing plate: stainless steel
Revolving screw feet: yes
Weighing space (WxDxH): 174 x 162 x 227 mm
Weighing surface (d): 91

Measuring system

Adjustment options: External calibration
Linearity: 0,300 mg
Minimum weight (USP): 400 mg
Readability [d]: 0,100 mg
Recommended adjusting weight: 80 g (E2)
Repeatability: 0,200 mg
Resolution: 820000
Stabilisation time under laboratory conditions: 3 s
Warm up time: 4 h
Weighing capacity [Max]: 82 g
Weighing units: g mg

Display

Display digit height (large): 1,400 cm

Counting

Counting resolution: 82000
Minimum piece weight at piece counting (Laboratory): 1 mg
Minimum piece weight at piece counting (Normal): 10 mg

KERN ACS80-4




The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]

Piktogramme

STANDARD



OPTION



FACTORY

