
# KERN CCS1T-4S







Measuring system	
Adjustment options:	External calibration
Linearity:	500 mg
Repeatability:	200 mg
Stabilisation time under laboratory conditions:	2 s
Weighing system:	Strain gauge
Weighing units:	lb kg

Display		
Display digit height (large):	2 cm	
Counting		

Counting	
Counting resolution:	15000000
Mininum piece weight at piece counting (Laboratory:	100 mg
Mininum piece weight at piece counting (Normal):	1 g
Reference weight:	yes

Functions		
Conversion function:	yes	
Counting function:	yes	
Function to save totals:	yes	
PRE-TARE function:	yes	
Weighing with tolerance range:	yes	

Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0°C
Minimum humidity:	0 %

Power supply	
Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	60 h
Operating time (Backlight on):	70 h

<u> </u>	<i>,</i>	
Services (	antian	
DELVICES		
00111000		C.,

Adjustment at the location of installation: abhängig von

Auflösung/Max | depends on resolution and capacity

DAkkS Certificate: 962-130-128

### Category

Brand: KERN

Product Group: Counting system

### Packaging & shipping

Delivery: 96 h

Dimensions packaging (WxDxH): 1050 x 1050 x 260 mm

Gross weight: 115 kg
Net weight: 110 kg

Shipping method: Freight forwarder

## Construction

1,500 m Cable length: Cable length of display device: 5 m Casing material: **Plastic** Dimensions housing (WxDxH): 320 x 350 x 125 mm Dimensions of weighing plate 1000 x 1000 x 108 mm (WxDxH): Level indicator: yes Material weighing plate: Metal lacquered Revolving screw feet: yes

1000 x 1000 mm

## <u>Piktogramme</u>

Weighing surface (WxD):

#### STANDARD



#### OPTION

