

KERN EG 220-3NM

The classic balance with robust tuning fork measuring system



Measuring system

Adjustment options:	Internal calibration (manual)
Linearity:	2 mg
Minimum weight (USP):	2 g
Readability [d]:	1 mg
Repeatability:	1 mg
Resolution:	220000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	220 g
Weighing units:	tl (HK) tol g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) ozt

Display

Display digit height (large):	1,700 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	20 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	II
Verification value [e]:	10 mg

Counting

Counting resolution:	220000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

Functions

Capacity display:	yes
Counting function:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	32 h
Operating time (Backlight on):	12 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-127
Verification:	965-216

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	320 x 410 x 230 mm
Gross weight:	3,200 kg
Net weight:	1,900 kg
Shipping method:	Parcel service

KERN EG 220-3NM




The classic balance with robust tuning fork measuring system

Construction

Casing material:	Plastic
Dimensions draft shield (WxDxH):	174 x 144 x 105 mm
Dimensions housing (WxDxH):	182 x 235 x 65 mm
Draft shield optional:	yes
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	158 x 130 x 78 mm
Weighing surface (d):	118

Piktogramme

STANDARD



OPTION



FACTORY

