

KERN EOE 150K50XL



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



Measuring system

| | |
|---|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 100 g |
| Readability [d]: | 50 g |
| Recommended adjusting weight: | 100 kg (M2) |
| Repeatability: | 50 g |
| Resolution: | 3000 |
| Stabilisation time under laboratory conditions: | 3 s |
| Tare range: | 150 kg |
| Warm up time: | 10 min |
| Weighing capacity [Max]: | 150 kg |
| Weighing system: | Strain gauge |
| Weighing units: | lb kg PCS |

Display

| | |
|-------------------------------|----------|
| Display digit height (large): | 2,500 cm |
|-------------------------------|----------|

Functions

| | |
|--|-----|
| Data hold function: | yes |
| Vibration-free weighing (Animal weighing program): | yes |

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 5 °C |

Power supply

| | |
|---------------------------------|--------------------------|
| Battery: | 4x1.5 V AA |
| Input voltage: | 100 V - 240 V 50 / 60 Hz |
| Mains adapter: | Mains adapter external |
| Mains adapter/adaptor included: | EURO CH UK US |
| Operating time: | 100 h |

Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand: KERN
Category: Balances

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 1015 x 565 x 85 mm
Gross weight: 20 kg
Net weight: 17,480 kg
Shipping method: Parcel service

Construction

Cable length of display device: 2 m
Casing material: plastic
Dimensions of display device (WxDxH): 235 x 114 x 51 mm
Dimensions of weighing plate (WxDxH): 950 x 500 x 58 mm
Material weighing plate: Steel lacquered
Revolving screw feet: yes
Wall mount: yes

Piktogramme

STANDARD



OPTION

