

KERN EOE 300K100XL



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand: KERN

Category: Balances

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 1060 x 550 x 100 mm

Gross weight: 19,500 kg

Net weight: 18 kg

Shipping method: Parcel service

Construction

Cable length of display device: 2 m

Casing material: plastic

Dimensions of display device (WxDxH): 235 x 114 x 51 mm

Dimensions of weighing plate (WxDxH): 950 x 500 x 58 mm

Material weighing plate: Steel lacquered

Revolving screw feet: yes

Wall mount: yes

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options: External calibration

Linearity: 200 g

Readability [d]: 100 g

Recommended adjusting weight: 200 kg (M2)

Repeatability: 100 g

Resolution: 3000

Stabilisation time under laboratory conditions: 3 s

Tare range: 300 kg

Warm up time: 10 min

Weighing capacity [Max]: 300 kg

Weighing system: Strain gauge

Weighing units: lb kg PCS

Display

Display digit height (large): 2,500 cm

Functions

Data hold function: yes

Vibration-free weighing (Animal weighing program): yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Battery: 4x1.5 V AA

Input voltage: 100 V - 240 V 50 / 60 Hz

Mains adapter: Mains adapter external

Mains adapter/adaptor included: EURO CH UK US

Operating time: 100 h