

# KERN EOE60K-2



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



## Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

## Category

Brand: KERN

Category: Balances

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 370 x 360 x 140 mm

Gross weight: 5 kg

Net weight: 3,900 kg

Shipping method: Parcel service

## Construction

Cable length of display device: 2 m

Casing material: plastic

Dimensions of display device (WxDxH): 235 x 114 x 51 mm

Dimensions of weighing plate (WxDxH): 315 x 305 x 57 mm

Material weighing plate: Steel lacquered

Wall mount: yes

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Adjustment options: External calibration

Linearity: 40 g

Readability [d]: 20 g

Recommended adjusting weight: 40 kg (M2)

Repeatability: 20 g

Resolution: 3000

Stabilisation time under laboratory conditions: 2,500 s

Tare range: 60 kg

Warm up time: 10 min

Weighing capacity [Max]: 60 kg

Weighing system: Strain gauge

Weighing units: lb kg PCS

## Display

Display digit height (large): 2,500 cm

## Functions

Data hold function: yes

Vibration-free weighing (Animal weighing program): yes

## Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

## Power supply

Battery: 4x1.5 V AA

Input voltage: 100 V - 240 V 50 / 60 Hz

Mains adapter: Mains adapter external

Mains adapter/adaptor included: EURO CH UK US

Operating time: 100 h