KERN **EWJ3000-2**



High-quality precision balance with automatic internal adjustment, also with EC type approval [M]



Measuring system				
Adjustment options:	Internal calibration (auto)			
Linearity:	50 mg			
Readability [d]:	10 mg			
Repeatability:	20 mg			
Resolution:	300000			
Stabilisation time under laboratory conditions:	3 s			
Warm up time:	2 h			
Weighing capacity [Max]:	3 kg			
Weighing system:	Strain gauge			
Weighing units:	tl (HK) g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) ozt			
Display				
Display digit height (large):	1,650 cm			
Counting				

Counting resolution:	150000		
Mininum piece weight at piece counting (Laboratory:	20 mg		
Mininum piece weight at piece counting (Normal):	200 mg		
Functions			
Capacity display:	yes		
Counting function:	yes		
Percentage determination:	yes		

Environmental conditions				
Maximum humidity:	80 %			
Maximum operating temperature:	35 °C			
Minimum ambient temperature:	15 °C			
Power supply				
Charging time:	12 h			
Input voltage:	100 V - 240 V 50 / 60 Hz			
Mains adapter:	Mains adapter external			
Mains adapter/adapter included:	EURO CH UK US			
Operating time (Backlight off):	20 h			
Operating time (Backlight on):	10 h			
Rechargeable battery:	Rchrg. battery optional - intern			
Services (optional)				
DAkkS Certificate:	963-127			
Category				
Brand:	KERN			
Category:	Balances			
Product Group:	Precision balance			
Packaging & shipping				
Delivery:	24 h			
Dimensions packaging (WxDxH):	390 x 280 x 270 mm			
Gross weight:	4,120 kg			
Net weight:	2,886 kg			
Shipping method:	Parcel service			
Construction				
Casing material:	Plastic			
Dimensions housing (WxDxH):	220 x 315 x 105 mm			
Level indicator:	yes			
Material weighing plate:	stainless steel			
Revolving screw feet:	yes			
Weighing surface (d):	120			

KERN **EWJ3000-2**



High-quality precision balance with automatic internal adjustment, also with EC type approval [M]

Piktogramme

STANDARD

		• 6884.•	•	GLP		_ ^	%	C	B
CA	L INT	RS 232	USB	PRINTER	PCS	RECIPE	PERCENT	UNIT	MULTI
Ľ	=1								
[DMS	1 DAY							

OPTION



FACTORY

