

# KERN FCB24K2

Bench scale with second display on the backside of the scale



## Measuring system

Adjustment options:	External calibration
Linearity:	6 g
Readability [d]:	2 g
Recommended adjusting weight:	20 kg (M1)
Repeatability:	2 g
Resolution:	12000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	30 min
Weighing capacity [Max]:	24 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol g mo lb dwt ffa oz tl (Tw) kg ozt

## Display

Display digit height (large):	2,500 cm
-------------------------------	----------

## Counting

Counting resolution:	6000
Minimum piece weight at piece counting (Laboratory):	4 g
Minimum piece weight at piece counting (Normal):	40 g

## Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	9 V Block
Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time:	12 h
Operating time (Backlight off):	10 h
Operating time (Backlight on):	5 h
Rechargeable battery:	Rchrg. battery optional

## Services (optional)

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	330 x 400 x 190 mm
Gross weight:	3,438 kg
Net weight:	2,600 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	270 x 323 x 110 mm
Dimensions of weighing plate (WxDxH):	252 x 228 x 12,5 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	253 x 227 mm


# KERN FCB24K2

Bench scale with second display on the backside of the scale



## Piktogramme

### STANDARD



### OPTION

