

KERN FCB8K0.1

Bench scale with second display on the backside of the scale



Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readability [d]:	100 mg
Recommended adjusting weight:	5 kg (F2); 2 kg (F2); 1 kg (F2)
Repeatability:	100 mg
Resolution:	80000
Stabilisation time under laboratory conditions:	3 s
Tare range:	8 kg
Warm up time:	2 h
Weighing capacity [Max]:	8 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol g mo lb dwt ffa oz tl (Tw) kg ozt

Display

Display digit height (large):	2,500 cm
-------------------------------	----------

Counting

Counting resolution:	40000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	9 V Block
Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time:	12 h
Operating time (Backlight off):	10 h
Operating time (Backlight on):	5 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	335 x 400 x 190 mm
Gross weight:	3,367 kg
Net weight:	2,600 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	270 x 323 x 110 mm
Dimensions of weighing plate (WxDxH):	252 x 228 x 12,5 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	253 x 227 mm


KERN FCB8K0.1



Bench scale with second display on the backside of the scale

Piktogramme

STANDARD



OPTION

