

KERN FOB3K-4NL



Stainless steel bench scale with large weighing range and IP67 protection against dust and water splashes



DAkkS Certificate: 963-127

Category

Brand: KERN
Category: Balances
Product Group: Bench scale

Packaging & shipping


Delivery: 24 h
Dimensions packaging (WxDxH): 420 x 305 x 180 mm
Gross weight: 4,265 kg
Net weight: 3,695 kg
Shipping method: Parcel service
UN number: 3496

Construction

Casing material: stainless steel
Dimensions housing (WxDxH): 295 x 260 x 95 mm
Material weighing plate: stainless steel
Weighing surface (WxD): 248 x 198 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options: External calibration
Linearity: 600 mg
Number of weighing ranges: 1
Readability [d]: 200 mg
Recommended adjusting weight: 3 kg (M1)
Repeatability: 200 mg
Resolution: 15000
Stabilisation time under laboratory conditions: 2 s
Warm up time: 30 min
Weighing capacity [Max]: 3 kg
Weighing system: Strain gauge
Weighing units: g lb

Display

Display digit height (large): 2,500 cm

Environmental conditions

Maximum humidity: 95 %
Maximum operating temperature: 35 °C
Minimum ambient temperature: 5 °C
Minimum humidity: 25 %

Power supply

Battery: 4x1.5 V AA
Input voltage: 230 V AC 50 Hz
Mains adapter/adapter included: EURO CH UK US
Operating time: 48 h

Services (optional)

Adjustment at the location of installation: 961-247