

# KERN HDB6K-3XL

Convenient, economical and always handy â now also as high-capacity XL-version



## Environmental conditions

Maximum humidity:	90 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	2x1.5 V AAA
Operating time:	180 h

## Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128H
--------------------	----------

## Category

Brand:	KERN
Product Group:	Hanging scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	75 x 150 x 225 mm
Gross weight:	430 g
Net weight:	200 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	107 x 25 x 101 mm
Overall dimensions mounted (WxDxH):	202 x 25 x 101 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Adjustment options:	External calibration
Linearity:	15 g
Precision (of [Max]):	0,500 %
Readability [d]:	5 g
Recommended adjusting weight:	5 kg (M1)
Repeatability:	5 g
Resolution:	1200
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	lb N kg

## Display

Display digit height (large):	1,200 cm
-------------------------------	----------

## Functions

Data hold function:	yes
---------------------	-----