

# KERN HFC3T-3



Compact crane scale for use in harsh environmental conditions or where space is limited, with convenient hand-held terminal



## Measuring system

Adjustment options:	External calibration
Linearity:	2 kg
Precision (of [Max]):	0,200 %
Readability [d]:	1 kg
Recommended adjusting weight:	3000 kg (M3)
Repeatability:	1 kg
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	lb N kg

## Display

Display digit height (large):	2,300 cm
-------------------------------	----------

## Functions

Data hold function:	yes
Peak function:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

## Services (optional)

Adjustment at the location of installation: 961-252

DAkkS Certificate: 963-132H

## Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

## Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	505 x 405 x 125 mm
Gross weight:	3,450 kg
Net weight:	2,150 kg
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	90 x 61 x 255 mm
Dimensions of display device (WxDxH):	88 x 64 x 256 mm

## Piktogramme

### STANDARD



### OPTION

