

KERN HFC5T-3



Compact crane scale for use in harsh environmental conditions or where space is limited, with convenient hand-held terminal



Measuring system

Adjustment options:	External calibration
Linearity:	4 kg
Precision (of [Max]):	0,200 %
Readability [d]:	2 kg
Recommended adjusting weight:	3000 kg (M3)
Repeatability:	2 kg
Resolution:	2500
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	5 t
Weighing system:	Strain gauge
Weighing units:	lb N kg

Display

Display digit height (large):	2,300 cm
-------------------------------	----------

Functions

Data hold function:	yes
Peak function:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Services (optional)

Adjustment at the location of installation: 961-252

DAkkS Certificate: 963-132H

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	405 x 505 x 125 mm
Gross weight:	5,800 kg
Net weight:	3,900 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Dimensions housing (WxDxH):	90 x 61 x 255 mm
Dimensions of display device (WxDxH):	88 x 64 x 256 mm

Piktogramme

STANDARD



OPTION

