

# KERN HFD3T-3M

Robust, high-resolution crane scale up to 12 t



Tare range:	2,999 t
Warm up time:	10 min
Weighing capacity [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height (large):	3 cm
-------------------------------	------

## Technical data about verification

Minimum load [Min]:	20 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	1 kg

## Functions

Standby function:	yes
-------------------	-----

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

## Power supply

Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

## Services (optional)

Adjustment at the location of installation: 961-252

DAkkS Certificate:	963-132H
Verification:	965-132H

## Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

## Measuring system

Adjustment options:	External calibration
Linearity:	1 kg
Precision (of [Max]):	0,200 %
Readability [d]:	1 kg
Repeatability:	1 kg
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s

# KERN HFD3T-3M

Robust, high-resolution crane scale up to 12 t



## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	725 x 275 x 270 mm
Gross weight:	12 kg
Net weight:	10 kg
Shipping method:	Parcel service
UN number:	3481

## Construction

Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	200 x 130 x 160 mm

## Piktogramme

### STANDARD



### OPTION



### FACTORY

