KERN IFB100K-3



High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg



Measuring system

Adjustment options:	External calibration		
Linearity:	15 g		
Load cell connection:	4-wire		
Readability [d]:	5 g		
Recommended adjusting weight:	150 kg (F2)		
Repeatability:	5 g		
Resolution:	30000		
Stabilisation time under laboratory conditions:	2 s		
Warm up time:	2 h		
Weighing capacity [Max]:	150 kg		
Weighing system:	Strain gauge		
Weighing units:	g lb lb:oz Hj. tJ kg		
Dioplay			

Display

Display digit height (large):

Counting		
Counting resolution:	30000	
Mininum piece weight at piece counting (Laboratory:	5 g	
Mininum piece weight at piece counting (Normal):	50 g	

5,200 cm

Functions

yes
yes
yes
yes

Environmental conditions				
Maximum humidity:	80 %			
Maximum operating temperature:	40 °C			
Minimum ambient temperature:	-10 °C			
Minimum humidity:	0 %			
Power supply				
Battery:	no battery			
Charging time:	12 h			
Input voltage:	100 V - 240 V 50 / 60 Hz			
Mains adapter:	Mains adapter external			
Mains adapter/adapter included:	EURO UK US			
Operating time (Backlight off):	35 h			
Operating time (Backlight on):	8 h			
Rechargeable battery:	Rchrg. battery optional			
Services (optional)				
Adjustment at the location of installation	on:961-249			
DAkkS Certificate:	963-129			
Category				
Brand:	KERN			
Category:	Balances			
Product Group:	Industiral scale			
Packaging & shipping				
Delivery:	24 h			
Dimensions packaging (WxDxH):	550 x 940 x 220 mm			
Gross weight:	12,800 kg			
Net weight:	11 kg			
Shipping method:	Parcel service			
Construction				
Cable length of display device:	3 m			
Casing material:	Plastic			
Dimensions of display device (WxDxH):	250 x 160 x 58 mm			
Dimensions of weighing plate (WxDxH):	500 x 400 x 130 mm			
of stand:	60 cm			
Level indicator:	yes			
Material weighing plate:	stainless steel			
Overall dimensions mounted (WxDxH):	660 x 400 x 760 mm			
Revolving screw feet:	yes			
Wall mount:	yes			
Weighing surface (WxD):	500 x 400 mm			

KERN IFB100K-3



High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg

Piktogramme

STANDARD

CAL EXT PROTOCOL	RS 232	GLP PRINTER	PCS	SUM	 MOVE	000 IP 65
OPTION DAkks +3 DAYS					 	

FACTORY

