# KERN IFB 15K2DM



High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg



Measuring system	
Adjustment options:	External calibration
Linearity:	2g 5g
Load cell connection:	4-wire
Readability [d]:	2g 5g
Recommended adjusting weight:	15 kg (F2)
Repeatability:	2g 5g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min   10 min
Weighing capacity [Max]:	6 kg   15 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display	
Display digit height (large):	5,200 cm

Technical data about verification	
Minimum load [Min]:	40 g   100 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2g 5g

Counting	
Counting resolution:	30000
Mininum piece weight at piece counting (Laboratory:	500 mg
Mininum piece weight at piece counting (Normal):	5 g

Functions		
Counting function:	yes	
Function to save totals:	yes	
Vibration-free weighing (Animal weighing program):	yes	
Weighing with tolerance range:	yes	
En income antal acquitions		

Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply	
Battery:	no battery
Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)		
Adjustment at the location of i	nstallation: 961-248	
DAkkS Certificate:	963-128	
Verification:	965-228	
Category		

Category	
Brand:	KERN
Category:	Balances
Product Group:	Industiral scale

Packaging & snipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	420 x 695 x 220 mm
Gross weight:	7,600 kg
Net weight:	5 kg
Shipping method:	Parcel service

Construction	
Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 58 mm
Dimensions of weighing plate (WxDxH):	300 x 240 x 110 mm

## KERN IFB 15K2DM



High-resolution scale in heavy version with EC type approval [M], now also up to [Max]  $600 \, \mathrm{kg}$ 

of stand: 33 cm

Level indicator: yes

Material weighing plate: stainless steel

Overall dimensions mounted (WxDxH):

Revolving screw feet: yes

Wall mount: yes

Weighing surface (WxD): 300 x 240 mm

### Piktogramme

#### STANDARD



#### **OPTION**



#### **FACTORY**

