

KERN IFB 300K50DM

High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg

KERN®



Measuring system

Adjustment options:	External calibration
Linearity:	50 g 100 g
Load cell connection:	6-wire
Readability [d]:	50 g 100 g
Recommended adjusting weight:	200 kg (M1)
Repeatability:	50 g 100 g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-300 kg
Warm up time:	10 min 10 min
Weighing capacity [Max]:	150 kg 300 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	5,200 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	1 kg 2 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	50 g 100 g

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	10 g
Minimum piece weight at piece counting (Normal):	100 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

Services (optional)

Adjustment at the location of installation:	961-249
DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	670 x 1050 x 245 mm
Gross weight:	24 kg
Net weight:	20 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 58 mm
Dimensions of weighing plate (WxDxH):	650 x 500 x 142 mm

KERN IFB 300K50DM




High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg

of stand:	60 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	810 x 500 x 820 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	650 x 500 mm

Piktogramme

STANDARD



OPTION



FACTORY

