

KERN IFB3K-4

High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Load cell connection:	4-wire
Readability [d]:	100 mg
Recommended adjusting weight:	3 kg (F2)
Repeatability:	100 mg
Resolution:	30000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-6 kg
Warm up time:	2 h
Weighing capacity [Max]:	3 kg
Weighing system:	Strain gauge
Weighing units:	g lb oz:Hj. tJ kg

Display

Display digit height (large):	5,200 cm
-------------------------------	----------

Counting

Counting resolution:	15000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Services (optional)

Adjustment at the location of installation:	961-247
DAkkS Certificate:	963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	415 x 700 x 240 mm
Gross weight:	7,030 kg
Net weight:	6 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 58 mm
Dimensions of weighing plate (WxDxH):	230 x 230 x 110 mm
of stand:	3,300 m
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	230 x 230 x 360 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	230 x 230 mm


KERN IFB3K-4



High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg

Piktogramme

STANDARD



OPTION



FACTORY

