

KERN IFS60K-2LM



Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution up to 75000 points - also with EC type approval [M]



Measuring system

Adjustment options:	External calibration
Linearity:	10 g 20 g
Load cell connection:	4-wire
Readability [d]:	10 g 20 g
Recommended adjusting weight:	60 kg (M1)
Repeatability:	10 g 20 g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	60 kg
Warm up time:	10 min 10 min
Weighing capacity [Max]:	30 kg 60 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	1,650 cm
Display digit height (small):	1,350 cm

Technical data about verification

Minimum load [Min]:	200 g 400 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	10 g 20 g

Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	1 g
Minimum piece weight at piece counting (Normal):	10 g
Reference weight:	yes

Functions

Counting function:	yes
Function to save totals:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Charging time:	12 h
Input voltage:	100-240V50/60Hz 190mA
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	18 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	930 x 545 x 210 mm
Gross weight:	14,650 kg
Net weight:	12,450 kg
Shipping method:	Parcel service

Construction

Cable length:	2,500 m
Cable length of display device:	3 m
Dimensions of display device (WxDxH):	260 x 150 x 65 mm
Dimensions of weighing plate (WxDxH):	500 x 400 x 120 mm

KERN IFS60K-2LM




Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution up to 75000 points - also with EC type approval [M]

of stand:	33 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	500 x 400 x 120 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	500 x 400 mm

Piktogramme

STANDARD



OPTION



FACTORY

