


KERN IOC60K-2M

All-round platform scale with a range of communication options and EC type approval [M]



Measuring system

Adjustment options:	External calibration
Linearisation (points):	3
Linearity:	30 g 60 g
Load cell connection:	4-wire
Readability [d]:	10 g 20 g
Recommended adjusting weight:	60 kg (M1)
Repeatability:	10 g 20 g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-60 kg
Warm up time:	10 min 10 min
Weighing capacity [Max]:	30 kg 60 kg
Weighing system:	Strain gauge
Weighing units:	g lb tJ HJ oz kg PCS

Display

Display digit height (large):	2,500 cm
Display digit height (small):	2,500 cm

Technical data about verification

Minimum load [Min]:	200 g 400 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	10 g 20 g

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	2 g
Minimum piece weight at piece counting (Normal):	20 g

Functions

Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	3 h
Input voltage:	100V-240V AC 50/60Hz 0,400 Amax
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO UK US
Operating time:	100 h
Operating time (Backlight off):	43 h
Operating time (Backlight on):	26 h
Rechargeable battery:	Rchrg. battery optional - intern

Services (optional)

Adjustment at the location of installation:	961-249
DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	810 x 350 x 180 mm
Gross weight:	8,800 kg
Net weight:	7,600 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	268 x 115 x 80 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 110 mm

KERN IOC60K-2M



All-round platform scale with a range of communication options and EC type approval [M]

Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm

Piktogramme

STANDARD



OPTION



FACTORY

