

# KERN IXS10K-3M



Platform scale with stainless steel display device with IP68 rating, XL display and EC type approval [M] – now also as high resolution version with high-resolution display



## Functions

Counting function:	yes
Data hold function:	yes
Peak function:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter/adaptor included:	EURO
Operating time (Backlight off):	80 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional (factory)

## Services (optional)

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 570 x 225 mm
Gross weight:	7 kg
Net weight:	5,100 kg
Shipping method:	Parcel service

## Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	232 x 150 x 80 mm
Dimensions of weighing plate (WxDxH):	300 x 240 x 86 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	2 g   5 g
Load cell connection:	4-wire
Number of weighing ranges:	2
Readability [d]:	2 g   5 g
Recommended adjusting weight:	15 kg (M1)
Repeatability:	2 g   5 g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-15 kg
Warm up time:	10 min   10 min
Weighing capacity [Max]:	6 kg   15 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height (large):	5,500 cm
-------------------------------	----------

## Technical data about verification

Minimum load [Min]:	40 g   100 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2 g   5 g

## Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	500 mg
Minimum piece weight at piece counting (Normal):	5 g

# KERN IXS10K-3M



Platform scale with stainless steel display device with IP68 rating, XL display and EC type approval [M] - now also as high resolution version with high-resolution display

Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	300 x 240 mm

## Piktogramme

### STANDARD

CAL EXT	PCS	SUM	TOL	MOVE	IP 65	IP 68	230 V	DMS
1 DAY	2 DAYS							

### OPTION

DAkkS
+3 DAYS

### FACTORY

RS 232	RS 485	BT	ACCU	M
				+3 DAYS