



Services (optional)	
DAkkS Certificate:	963-127
Category	
Brand:	KERN
Category:	Balances
Product Group:	Precision balance
Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	238 x 357 x 180 mm
Gross weight:	2,200 kg
Net weight:	1 kg
Shipping method:	Parcel service
Construction	
Casing material:	Plastic
Dimensions draft shield (ÃxH):	106 42
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Level indicator:	yes
Overall dimensions mounted (WxDxH):	167 x 250 x 123 mm
Revolving screw feet:	yes
Weighing space (ÃxH):	90 40
Weighing surface (d):	81

Piktogramme

STANDARD



OPTION

	DAkkS
ACCU	+3 DAYS

U	
Adjustment options:	External calibration
Linearity:	5 mg
Readability [d]:	1 mg
Recommended adjusting weight:	300 g (E2)
Repeatability:	2 mg
Resolution:	360000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	360 g
Weighing system:	Strain gauge
Weighing units:	tl (HK) g tl (Cn) lb * tl (Singap. Malays) dwt ct oz tl (Tw) gn kg t to

Display

Display digit height (large):

Measuring system

Counting		
Counting resolution:	360000	
Mininum piece weight at piece counting (Laboratory:	1 mg	
Mininum piece weight at piece counting (Normal):	10 mg	

9 mm

Functions

Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional