

KERN MFB 150K100S05



Design body analysis scale to determine body weight, body fat, body fluid, muscle mass, proportion of bone, BMI and metabolic rate/metabolic rate when exercising



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	330 x 330 x 300 mm
Gross weight:	10 kg
Net weight:	8,200 kg
Shipping method:	Parcel service
UN number:	3091

Construction

Dimensions of weighing plate (WxDxH):	300 x 300 x 25 mm
Overall dimensions mounted (WxDxH):	300 x 300 x 25 mm
Weighing surface (WxD):	300 x 300 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	Calibration not possible
Linearity:	500 g
Readability [d]:	100 g
Repeatability:	100 g
Resolution:	1820
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	182 kg
Weighing system:	Strain gauge
Weighing units:	lb kg

Display

Display digit height (large):	3,500 cm
-------------------------------	----------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

Power supply

Battery:	2xCR2032
Operating time:	100 h

Category

Brand:	KERN
Product Group:	Personal floor scale