

# KERN MPB300K100P

Personal floor scale with BMI function



## Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Readability [d]:	100 g
Recommended adjusting weight:	250 kg (M1)
Repeatability:	100 g
Resolution:	3000
Warm up time:	10 min
Weighing capacity [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height (large):	2,500 cm
-------------------------------	----------

## Functions

BMI function:	yes
Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	6x1.5 V AA
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time:	170 h

## Services (optional)

Adjustment at the location of installation: 961-249

DAkKS Certificate: 963-129

## Category

Brand:	KERN
Category:	Balances
Product Group:	Personal floor scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	1175 x 410 x 330 mm
Gross weight:	10 kg
Net weight:	6,400 kg
Shipping method:	Parcel service

## Construction

Casing material:	Steel lacquered
Dimensions of display device (WxDxH):	210 x 110 x 45 mm
Dimensions of weighing plate (WxDxH):	315 x 300 x 55 mm
of stand:	1 m
Material weighing plate:	Steel lacquered
Overall dimensions mounted (WxDxH):	315 x 450 x 1000 mm

## Piktogramme

### STANDARD



### OPTION

