

# KERN MPI200K-1S05



Personal scale with particularly large, flat weighing plate to make it easier to step on and give maximum safety



## Construction

Casing material:	plastic
Dimensions of weighing plate (WxDxH):	430 x 370 x 50 mm
Material weighing plate:	Plastic
Weighing surface (WxD):	430 x 370 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Adjustment options:	Calibration not possible
Linearity:	500 g
Readability [d]:	100 g
Repeatability:	100 g
Resolution:	2000
Warm up time:	10 min
Weighing capacity [Max]:	200 kg
Weighing system:	Strain gauge
Weighing units:	lb kg

## Display

Display digit height (large):	3 cm
-------------------------------	------

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

## Power supply

Battery:	4x 1.5V AAA
Operating time:	20 h

## Category

Brand:	KERN
Product Group:	Personal floor scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	510 x 420 x 415 mm
Gross weight:	17,700 kg
Net weight:	7,500 kg
Shipping method:	Parcel service