

KERN PCD6K-4

High-resolution precision balance with removable display for maximum flexibility



Functions

Counting function:	yes
Peak function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	9 V Block
Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time:	12 h
Operating time (Backlight off):	24 h
Operating time (Backlight on):	12 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 360 x 160 mm
Gross weight:	2,175 kg
Net weight:	1,700 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	1,200 m
Casing material:	Plastic
Dimensions device (WxDxH):	165 x 280 x 75 mm
Dimensions housing (WxDxH):	165 x 280 x 75 mm
Dimensions of display device (WxDxH):	140 x 46 x 75 mm
Dimensions of weighing plate (WxDxH):	161 x 161 x 7 mm

Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readability [d]:	100 mg
Recommended adjusting weight:	6 kg (F1)
Repeatability:	100 mg
Resolution:	60000
Stabilisation time under laboratory conditions:	3 s
Tare range:	6 kg
Warm up time:	2 h
Weighing capacity [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol g mo tl (Singap. Malays) dwt ffa ct oz gn ozt

Display

Display digit height (large):	2,100 cm
-------------------------------	----------

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	200 mg
Minimum piece weight at piece counting (Normal):	2 g

KERN PCD6K-4



High-resolution precision balance with removable display for maximum flexibility

of stand:	25 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	165 x 280 x 75 mm
Revolving screw feet:	yes
Weighing surface (WxD):	160 x 160 mm

Piktogramme

STANDARD



OPTION

