





Ver	Date	Modify Contents	Issue	Confirm
A01	2021-08-13	----		



ITEMS	FEATURES	ITEMS	FEATURES
LCD TYPE	FSTN	LIFE VERSION	Long life design
DISPLAY MODE	Positive	POLARIZER	Transflective
BKL TYPE	Edge Type	BKL COLOR	RGB
VIEWING	6:00 ↑	V _{lc} m(V _{dd} ~ V _{ss})	5.0V
DC-DC	Without	V _{lcd} (V _{dd} ~ V ₀)	4.5V
OP.TEMP	-20° C ~ 70° C	V _{ed} (LED+ ~ LED-)	5.0V
ST.TEMP	-30° C ~ 80° C	REMARK	NONE
Il _{ed} @ V _{led}	NONE		

PIN	SIGNAL	PIN	SIGNAL	PIN	SIGNAL
1	VSS	9	DB2	17	K(G)
2	VDD	10	DB3	18	K(R)
3	V0	11	DB4		
4	RS	12	DB5		
5	R/W	13	DB6		
6	E	14	DB7		
7	DB0	15	A		
8	DB1	16	K(B)		

DRAWING	MD21605A6W-FPTLRGB	PRODUCT	MD21605A6W-FPTLRGB
QC DOC.	MD21605A6W-FPTLRGB	OEM CODE	-----

MIDAS

UNDECLARED TOLERANCE: .X ±0.20 .XX ±0.10

UNIT:mm
PAGE:1/1
ROHS