



Quick Disconnect Thermocouples with Removable Miniature Connectors

Item# SCP316SS-125U-4

- Also Available with M12 and M8 style connectors
- Glass Filled Nylon Connector Body Rated to 220°C (425°F)
- 304, 310, 316, 321 SS, Inconel, or Super OMEGACLAD™ XL Sheath
- Standard 6 and 12" Lengths Available
- Sheath Diameters from 0.010 to 0.125"
- Smallest Diam 0.010 Available in J, K, T Only
- Grounded, Ungrounded, or Exposed Junction
- Color-Coded SMP Miniature Connector Termination
- Mating Connector, Cable Clamp, and Locking Clip sold Separately
- LCP and Ceramic Connectors Available
- Custom Length Available
- Cal-5 Available

Product Details

OMEGA's Quick Disconnect Thermocouples with Miniature Connectors are high quality, economical thermocouple probes. They feature a glass filled nylon connector which is rated for temperatures up to 220°C (425°F). The probes are available in with diameters as small as 0.25mm (0.010 inches) and as large as to 3.0mm (0.125 inches).