

The Zyklop Ratchet

Faster than a speeding bullet.

8000 C Zyklop ratchet with 1/2" drive



Applications: For 1/2" square drive sockets and 1/2" adapters with square drive, with ball lock

Design: Rotating mass design and handy freewheel sleeve for faster work; swivelling ratchet head; defined lock positions at 0°, 15°, 90° right and left; at 0° it can be used like a conventional screwdriver; pushbutton release; CW/ACW toggle, fine-pitched tooth design, with small return angle of 5°

Handle: Multicomponent Kraffform handle for comfort and torque

Code	1/2"	mm	1
05003600001	1/2"	277,0	1

8790 HMC Zyklop socket with 1/2" drive



Applications: For hex-head fasteners

Design: For manual and (non-impact) machine applications, with ball intercept ring, rear end knurling for reliable manual precision, chrome vanadium, brushed chromium plated

? How can I avoid buying many different ratchets?



Thanks to its intelligent construction the Zyklop can be used as a fine-tooth ratchet, flex-head ratchet, angle ratchet, quick-release ratchet and power ratchet. When locked in a 0° position the tool can even be used as a screwdriver. Zyklop saves space, weight, cost and time!

Code	mm	mm	mm	mm	mm	mm	mm
05003601001	10,0		37,0	15,5	24,0	17,0	1
05003602001	11,0		37,0	16,5	24,0	17,0	1
05003603001	12,0		37,0	17,5	24,0	17,0	1
05003604001	13,0		37,0	19,0	24,0	17,0	1
05003605001	14,0		37,0	20,0	24,0	17,0	1
05003606001	15,0		37,0	21,0	24,0	17,0	1
05003607001	16,0		37,0	22,5	24,0	17,0	1
05003608001	17,0		37,0	24,0	26,0	17,0	1
05003609001	18,0		37,0	25,0	26,0	17,0	1
05003610001	19,0		37,0	26,5	26,0	20,0	1
05003611001	20,0		37,0	28,0	26,0	20,0	1
05003612001	21,0		37,0	29,0	26,0	20,0	1
05003613001	22,0		37,0	30,5	26,0	20,0	1
05003614001	24,0		37,0	33,0	28,0	20,0	1
05003615001	27,0		40,0	36,5	32,0	23,0	1
05003616001	30,0		42,0	40,0	34,0	25,0	1
05003617001	32,0		42,0	42,0	36,0	25,0	1
05003618001		3/8"	37,0	15,5	24,0	17,0	1
05003619001		7/16"	37,0	16,5	24,0	17,0	1
05003620001		1/2"	37,0	19,0	24,0	17,0	1
05003621001		9/16"	37,0	20,0	24,0	17,0	1
05003622001		19/32"	37,0	21,0	24,0	17,0	1
05003623001		5/8"	37,0	22,5	24,0	17,0	1
05003624001		11/16"	37,0	25,5	26,0	17,0	1
05003625001		3/4"	37,0	26,5	26,0	20,0	1
05003626001		25/32"	37,0	28,0	26,0	20,0	1
05003627001		13/16"	37,0	29,0	26,0	20,0	1
05003628001		7/8"	37,0	30,5	26,0	20,0	1
05003629001		15/16"	37,0	33,0	28,0	20,0	1
05003630001		31/32"	37,0	33,0	28,0	20,0	1
05003631001		1"	40,0	36,5	32,0	23,0	1
05003632001		1 1/16"	40,0	36,5	32,0	23,0	1
05003633001		1 1/8"	40,0	40,0	34,0	23,0	1
05003634001		1 3/16"	42,0	40,0	34,0	25,0	1
05003635001		1 1/4"	42,0	42,0	36,0	25,0	1